


SPECIFICATION:

Material	Nylon PA
Protection rating	IP 68 (with sealing)
Temperature range	-40...+100 °C



PRODUCT RANGE:

Art. Nr.	Thread	Clamping range	Colour	GL	H	AG	Spanner size	Panel mounting hole
RND 465-00815	PG11	5...10 mm	Grey	8 mm	35 mm	18.6 mm	22 mm	18.6-18.9 mm
RND 465-00816	PG13.5	6...12 mm	Grey	9 mm	37 mm	20.4 mm	24 mm	20.4-20.7 mm
RND 465-00817	PG16	10...14 mm	Grey	10 mm	38 mm	22.5 mm	27 mm	22.5-22.8 mm
RND 465-00818	PG21	13...18 mm	Grey	10 mm	42 mm	28.3 mm	33 mm	28.3-28.6 mm
RND 465-00819	PG11	5...10 mm	Black	8 mm	35 mm	18.6 mm	22 mm	18.6-18.9 mm
RND 465-00820	PG13.5	6...12 mm	Black	9 mm	37 mm	20.4 mm	24 mm	20.4-20.7 mm
RND 465-00821	PG16	10...14 mm	Black	10 mm	38 mm	22.5 mm	27 mm	22.5-22.8 mm
RND 465-00822	PG21	13...18 mm	Black	10 mm	42 mm	28.3 mm	33 mm	28.3-28.6 mm
RND 465-00823	M14 x 1.5	4...8 mm	Grey	8 mm	31 mm	14 mm	19 mm	14-14.3 mm
RND 465-00824	M16 x 1.5	4...8 mm	Grey	8 mm	31 mm	16 mm	19 mm	16-16.3 mm
RND 465-00825	M18 x 1.5	5...10 mm	Grey	8 mm	35 mm	18 mm	22 mm	18-18.3 mm
RND 465-00826	M20 x 1.5	6...12 mm	Grey	9 mm	37 mm	20 mm	24 mm	20-20.3 mm
RND 465-00827	M22 x 1.5	10...14 mm	Grey	10 mm	38 mm	22 mm	27 mm	22-22.3 mm
RND 465-00828	M25 x 1.5	13...18 mm	Grey	10 mm	42 mm	25 mm	33 mm	25-25.3 mm
RND 465-00829	M27 x 1.5	13...18 mm	Grey	10 mm	42 mm	27 mm	33 mm	27-27.3 mm
RND 465-00830	M32 x 1.5	18...25 mm	Grey	12 mm	50 mm	32 mm	41/42 mm	32-32.3 mm
RND 465-00831	M40 x 1.5	22...32 mm	Grey	14 mm	60 mm	40 mm	52/53 mm	40-40.3 mm
RND 465-00832	M14 x 1.5	4...8 mm	Black	8 mm	31 mm	14 mm	19 mm	14-14.3 mm
RND 465-00833	M16 x 1.5	4...8 mm	Black	8 mm	31 mm	16 mm	19 mm	16-16.3 mm
RND 465-00834	M18 x 1.5	5...10 mm	Black	8 mm	35 mm	18 mm	22 mm	18-18.3 mm
RND 465-00835	M20 x 1.5	6...12 mm	Black	9 mm	37 mm	20 mm	24 mm	20-20.3 mm
RND 465-00836	M22 x 1.5	10...14 mm	Black	10 mm	38 mm	22 mm	27 mm	22-22.3 mm
RND 465-00837	M25 x 1.5	13...18 mm	Black	10 mm	42 mm	25 mm	33 mm	25-25.3 mm
RND 465-00838	M27 x 1.5	13...18 mm	Black	10 mm	42 mm	27 mm	33 mm	27-27.3 mm
RND 465-00839	M32 x 1.5	18...25 mm	Black	12 mm	50 mm	32 mm	41/42 mm	32-32.3 mm
RND 465-00840	M40 x 1.5	22...32 mm	Black	14 mm	60 mm	40 mm	52/53 mm	40-40.3 mm