

## 230 LED Installaton Beacon

LED Permanent beacon with M 20 thread for applications such as position and cable operated switches. Extremely high light intensity. Modern Chip-On-Board technology. Ideal for installation in limited space due to short thread. High protection rating IP 65 for indoor and outdoor applications.



### TECHNICAL SPECIFICATIONS

---

<b>Dimensions (Diameter x Height):</b>	28,7 mm x 38,5 mm
<b>Dome:</b>	Polycarbonate, transparent
<b>Fixing :</b>	Installation mounting for M 20 x 1,5 mm
<b>Housing :</b>	ABS/PC-Blend, black
<b>Operating voltage:</b>	24 V =, 115 V ~, 230 V ~
<b>Current consumption:</b>	45 mA at 24 V 15 mA at 115 V 15 mA at 230 V
<b>Starting current:</b>	< 0,5 A at 24 V
<b>Life duration:</b>	up to 100.000 h
<b>Terminal element :</b>	2 wires, c. 115 mm long



## 230 LED Installaton Beacon

LED Permanent beacon with M 20 thread for applications such as position and cable operated switches. Extremely high light intensity. Modern Chip-On-Board technology. Ideal for installation in limited space due to short thread. High protection rating IP 65 for indoor and outdoor applications.



### ORDER SPECIFICATIONS

---

	24 V =	115 V ~	240 V ~
red	23010055	23010067	23010068
yellow	23030055	23030067	23030068
clear	23040055	23040067	23040068