

SMX2000RMLV2U

APC Smart-UPS X, Line Interactive, 2000VA, Rack/tower convertible 2U, 120V, 3x 5-15R+3x 5-20R+1x L5-20R NEMA, SmartSlot, Extended runtime



Overview

Lead time Usually Ships within 2 Weeks



Main

Main Input Voltage	120 V
Other Input Voltage	100 V 110 V 127 V
Main Output Voltage	120 V
Other Output Voltage	100 V 110 V 127 V
Kw Rating	1800 W
Rated power in VA	1920 VA
Input Connection Type	NEMA 5-20P
Nb of power socket outlets	3 NEMA 5-15R 3 NEMA 5-20R 1 NEMA L5-20R
Number of rack unit	2U
Cable length	8 ft (2.44 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack Mounting brackets Rack Mounting support rails Removable support feet Smart UPS signalling RS-232 cable USB cable

General

Number of power module	1750
Number of power module filled slots	0
Number of power module free slots	0
Product web sub-family	Extended run
Redundant	No

Physical

Color	Black
Height	3.35 in (8.5 cm)
Width	17.01 in (43.2 cm)
Depth	26.26 in (66.7 cm)
Net Weight	84.77 lb(US) (38.45 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	75...154 V adjustable 70...153 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	1920 VA
Max Configurable Power (Watts)	1800 W
Transfer Time	2-4 ms 4ms typical : 8ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	BSMI CSA NOM TÜV VCCI Class A
Equipment protection policy	Lifetime : \$150000
Standards	EN 50091-2 EN 55022 Class A FCC Part 15 class A UL 1778

Environmental

Acoustic level	55 dBA
Heat dissipation	203 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery Life	3...5 year(s)

Battery power in VAH	690 VAh runtime
Battery Charge Power (Watts)	229 W rated
Battery option	SMX120RMBP2U 1 2070 VAh SMX120RMBP2U 2 3450 VAh SMX120RMBP2U 3 4830 VAh SMX120RMBP2U 4 6210 VAh SMX120RMBP2U 6 8970 VAh SMX120RMBP2U 8 11730 VAh SMX120RMBP2U 10 14490 VAh

Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators Multi-function LCD status and control console
Emergency Power Off (EPO)	Yes
Free slots	1

Surge Protection and Filtering

Surge energy rating	540 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304268536
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No

Packing Units

Package 1 Height	9.57 in (24.3 cm)
Package 1 width	23.46 in (59.6 cm)
Package 1 Length	34.21 in (86.9 cm)
Number of Units in Package 3	8
Package 3 Weight	856.92 lb(US) (388.69 kg)
Package 3 Length	39.37 in (100 cm)
Pallet unit layers	2
Pallet layers	4

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty

3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMX2000RMLV2U](#)