

# KERN EWJ3000-2



High-quality precision balance with automatic internal adjustment, also with EC type approval [M]



## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	15 °C

## Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time (Backlight off):	20 h
Operating time (Backlight on):	10 h
Rechargeable battery:	Rchrg. battery optional - intern

## Service

DAkkS Certificate:	963-127
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	390 x 280 x 270 mm
Gross weight:	4,120 kg
Net weight:	2,886 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	220 x 315 x 105 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (d):	120

## Measuring system

Adjustment options:	Internal calibration (auto)
Linearity:	50 mg
Readability [d]:	10 mg
Repeatability:	20 mg
Resolution:	300000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	2 h
Weighing capacity [Max]:	3 kg
Weighing system:	Strain gauge
Weighing units:	ozt tl (HK) mo lb tl (Singap. Malays) ct dwt oz tl (Tw)

## Display

Display digit height (large):	1,650 cm
-------------------------------	----------

## Counting

Counting resolution:	150000
Minimum piece weight at piece counting (Laboratory):	20 mg
Minimum piece weight at piece counting (Normal):	200 mg

## Functions

Capacity display:	yes
Counting function:	yes
Percentage determination:	yes

# KERN EWJ3000-2



High-quality precision balance with automatic internal adjustment, also with EC type approval [M]

## Piktogramme

### STANDARD



### OPTION



### FACTORY

