



Sample photo

Order symbol: ALN 082506
Product nbr: 7811190
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016096
EI. number:
Finland: 3420047
Electric No. Sweden: 2536317

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:			Accessories:		
Length	Width	Height			
mm:	252	81	57	AM 0813	Mounting plate
inch:	9.9	3.2	2.2	AM 0818	Mounting plate
Materials:			AM 0825	Mounting plate	
Material:	Aluminium		ARM 0808	DIN-15 Mounting rail	
Base colour:	RAL 7001		ARM 0825	DIN-15 Mounting rail	
Cover screws material:	Stainless steel		ARH 26	DIN-35 Mounting rail	
Cover colour:	RAL 7001		MR 75003	Selftapping tapite screw M3	
Gasket material:	Polyurethane		MRS 28540	Wall fastening lug (2 pcs)	
Temperatures:			Rating:		
Temperature °C (short term):	-50 ... 140 °C			Ingress Protection (EN 60529): IP66/IP67/IP68	
Temperature °C (continuous):	-50 ... 80 °C			Impact Resistance (EN 62262): IK08	
Temperature °F (short term):	-60 ... 285 °F			NEMA Class: NEMA 1, 4, 4X, 12, 13	
Temperature °F (continuous):	-60 ... 175 °F				
Accessories:			Certificates:		
AM 0808	Mounting plate			SGS Fimko	

