

ARCA 403021



Sample photo

Order symbol: ARCA 403021
Product nbr: 8120007
Description: Cabinet, PC
Remarks: Grey cover, 2-point locking, hinges on the long side

EAN: 6418074079183
EI. number:
 Finland: 3423054
 Denmark: 8212091058
 Sweden: 2500114
 Norway:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
mm:		400	300	210	Ingress Protection (EN 60529): IP 66
inch:		15.7	11.8	8.3	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Gasket material:		PUR			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MPS ARCA 4030		Mounting plate			
MPP ARCA 4030		Mounting plate perforated			
MPX ARCA 4030		Mounting plate			
DRS ARCA 403015		DIN rail frame set			
DRS ARCA 403021		DIN rail frame set			
IDS ARCA 4030		Inner door set			
PMK ARCA 30		Pole mounting kit			
Certificates:					
Fimko					

ARCA 400x300x150-210

ARCA 300x400x150-210

