




DESCRIPTION: 988 SERIES BACK SHELL KIT




STRAIN
RELIEF
CLAMP



STRAIN
RELIEF
SCREW



BACK
SHELL
SCREW



SPRING
CLIP

No. OF PINS	DIMENSIONS					
	A	B	C	D	E	F
50	1.988 [50.50]	1.594 [40.50]	0.422 [10.71]	0.498 [12.65]	0.354 [9.00] - 0.433 [11.00]	1.445 [36.70]
68	2.409 [61.20]	2.020 [51.30]	0.421 [10.70]	0.480 [12.20]	0.433 [11.00] - 0.551 [14.00]	2.453 [36.90]
ALL TOLERANCES = 0.012 [0.30]						

MATERIAL:

- BACK SHELL: ZINC PLATED NICKEL OVER COPPER
JACKSCREWS: STEEL, NICKEL PLATED OVER COPPER
SCREWS: STEEL, NICKEL PLATED OVER COPPER
CLAMP: STEEL, NICKEL PLATED

KIT INCLUDES:

- 2-BACK SHELL HALVES
1-STRAIN RELIEF CLAMP
1-CONNECTOR (SOLDER LATCH)
2-STRAIN RELIEF SCREWS
(FLAT HEAD M2.6)
2-BACK SHELL SCREWS
(FLAT HEAD M2.6)
2-SPRING CLIPS

BACK SHELL KIT
PART NUMBER
988-YYY-130L121

- SERIES _____
POSITIONS _____
050 _____
068 _____
CONTACTS _____
SOLDER _____
MATERIAL _____
30 = DIE CAST (NICKEL)
RoHS COMPLIANT _____
L = LOW TEMP. PROCESS _____
COLOR _____
12 = METAL(IZED)
PUT-UP _____
1 = KIT

RoHS COMPLIANT

UNITS = INCHES [MM] DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		SCALE: NTS	SHEET 1	OF 3	REV 5
		DATE: 04/18/2008		DWG NO. 988-YYY-130L121			

DESCRIPTION: CONNECTOR FOR 988 SERIES BACK SHELL KIT




No. OF PINS	DIMENSIONS		
	A	B	C
50	1.545 [39.30]	1.372 [34.85]	0.366 [9.30]
68	1.996 [50.70]	1.825 [46.35]	0.366 [9.30]

MATERIAL:

HOUSING: THREMOPLASTIC, BLACK, P.B.T. UL94V-0
CONTACTS: PHOSPHOR BRONZE, 5u" GOLD MATING AREA 100u" MIN TIN SOLDER AREA
FRONT SHELL: STEEL, NICKEL PLATED OVER COPPER

ELECTRICAL:

CURRENT RATING: 1 AMPS
INSULATOR RESISTANCE: 500 MOHMS Min.
DIELECTRIC WITHSTANDING: 500VAC
CONTACT RESISTANCE: 35 mOhms Max.
OPERATING TEMPERATURE: -55° ~ +85° C






RoHS COMPLIANT




UNITS = INCHES [MM] DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		SCALE: NTS	SHEET 2	OF 3	REV 5
		DATE: 04/18/2008		DWG NO.	988-YYY-130L121		

50 POSITION



68 POSITION



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

C. SMITH

DATE:

04/18/2008

UNITS = INCHES [MM] DO NOT SCALE FROM DRAWING

NorComp

SCALE:

NTS

SHEET

OF

3

3

REV

5

DWG NO.

988-YYY-130L121

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[988-068-130L121](#)