


US Power Supply Cord with IEC Connector C19, straight



**Description**

- 1 Function:
- Power Cord, Protection class I
- Pin temperature 70 °C
- custom specific versions on request

**Weblinks**

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#)

**Technical Data**

Ratings UL/CSA	15 A / 125 VAC; 50/60Hz	Connector	C19 acc. to IEC 60320
Allowable Operation Temp.	-40°C to 70°C		UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 16A, Protection Class I
Degree of Protection	from front side IP 40 acc. to IEC 60529		
Protection Class	Suitable for appliances with protection class I acc. to IEC 61140		
Material: Housing	black		

**All Variants**

Connector		cable				Plug					Order Number
Type	V-Lock	Cord Type	Conductor cross section	Length [m]	Color	Type	Country	Standard	Style	Index	
C19		SJT 3x14 AWG	3 x 14 AWG	2.5	black	North America	USA	NEMA 5-15	-	-	6009.5195

Most Popular.

Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

**Packaging unit** 25 Pcs

**Mating Inlets/Plugs**

**Category / Description**

[Appliance Inlet Overview complete](#)



IEC Appliance Inlet C20, Screw-on Mounting, Rear Side, PCB Terminal	1601
IEC Appliance Inlet C20, Screw-on Mounting, Front Side, Solder or Quick-connect Terminal	4798
IEC Appliance Inlet C20, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal	4793
IEC Appliance Inlet C24, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal	4794
IEC Appliance Inlet C20, Screw-on Mounting, Front Side, Solder, Quick-connect or Screw Terminal	1621

[Appliance Inlet further types to Cord Sets 15 A](#)



## Appliance inlets/-outlets Overview complete

Plug Coupler IEC C20 / IEC J, Screw-on Mounting	4730
---	------

[Appliance inlets/-outlets further types to Cord Sets 15 A](#)



## Plug Overview complete

IEC Plug I, Cord Connector (Rewireable), Straight	4796
---	------

IEC Plug I, Cord Connector (Rewireable), Angled	4789
---	------

[Plug further types to Cord Sets 15 A](#)



## Power Entry Module Overview complete

IEC Appliance Inlet C20 with Line Switch, 2-pole	EC11
--	------

IEC Appliance Inlet C20 with Circuit Breaker TA35 1-pole	6136
--	------

IEC Appliance Inlet C20 with Circuit Breaker TA45	EF11
---	------

[Power Entry Module further types to Cord Sets 15 A](#)



## Power Entry Module with line filter Overview complete

IEC Appliance Inlet C20 with Filter, Line Switch 2-pole	EC12
---	------

IEC Appliance Inlet C20 with Filter, Circuit Breaker TA45 (recessed)	EF12
--	------

IEC Appliance Inlet C20 with Filter, Front or Rear Side Mounting	C20F
--	------

[Power Entry Module with line filter further types to Cord Sets 15 A](#)