




HDB 15 Male  
Plastic: Blue



HDB 15 Male  
Plastic: Blue



**Material:**

.CABLE:28AWG(7/0.127 T.C)\*3COAX(75 OHMS)+INSULATION:FO-PE INNER  
JACKET:PVC OD:Ø2.5± 0.1mm(UL-1354)+28AWG(7/0.127 T.C)\*4C+  
INSULATION:SR-PVC ID:Ø0.85± 0.05mm(UL-1061)+AL/MY+DRAIN  
WIRE:26AWG(7/0.16 T.C)+BRAID SHIELD(85%)+OUTER JACKET:PVC  
COLOR:BEIGE OD:Ø8.1± 0.15mm UL-2919

**.CONNECTOR:**

P1&P2:HDB 15P MALE,GOLD FLASH CONTACT,NICKEL PLATED SHELL  
(9TH PIN UNLOAD)

.SHIELD:COPPER-FOIL 360° SOLDER TO CONNECTOR SHELL & CABLE BRAID  
.HOOD:MOLDED TYPE,PVC 45P,COLOR:BEIGE.


**.ELECTRONIC TEST:**

- <1>.100% OPEN SHORT & MIS WIRE TEST
- <2>.CONTACT RESISTANCE 3 OHMS MAX.
- <3>.INSULATION RESISTANCE 1M OHMS MIN/ DC 5V

**.PACKING:SEE P-0039 REV.C PACKING DRAWING**

(HANKING SIZE MUST BE SMALLER THAN PACKING)  
PACKING TYPE: DB VP4.

**PIN OUT**



Scale	1:1						Name	Item No.
TOLERANCE								<b>AK3760-3-R</b>
X.X	±0.40				Drawn	10/26/12	Miller	
X.XX	±0.25				Approved	10/26/12	Groll	
X.XXX	±0.15							
Angle	±3°							
								<b>rev00</b>
								Sheet

