Multi-purpose cutters



←a→		←b→		↓ max. ↑	۵ <u>۲</u> ۵	Ø	
mm	"	mm	"	mm	kg	qty.	V5
200	8	50	2	0,6	0.27	10	
	mm	mm "	mm "mm		mm " mm " mm	mm " mm " mm kg	mm mm mm kg qty.





- Cutting edge and handle forged in one piece for high stability
- Edges with serrations for slip-proof working
- ERGO-handle for increased comfort reduced hand fatigue!
- Blades are sandblasted and chromiumplated for corrosion protection
- Cuts cold-rolled steel up to 0.6 mm thick
- On carded hang pack

Multi-purpose cutters MULTISNIP Master

Nº	←a→		←b→		↓ max. ↑	5	Ø	
	mm	"	mm	"	mm	kg	qty.	V5
D51A	235	9 1/4	50	2	0,4	0.19	5	



Multi-purpose cutters Combinox

Nº	←a→		÷	b→	5	Ø	
	mm	"	mm	"	kg	qty.	V5
D50	190	7 1/2	40	1 9/16	0.14	10	



 All metal parts are made of stainless steel

■ For long continuous straight and curved

- Handle made of robust fibreglassreinforced plastic with a soft material insert
- On carded hang pack

cuts

- Stainless steel blades
- Ergonomically designed handles with soft-insert
- With wire guide for cutting binding wire to Ø 2.5 mm
- Circular cutting to stop for stripping cable from Ø 1.0 to 1.5 mm
- On carded hang pack