



DATE	REV	ECN	APP'D. BY
10/20/20	A0	RELEASED	ADB
-	-	-	-




NOTES:

- COMPLIANT WITH DISPLAYPORT 1.4 SPECIFICATION.
- CONNECTOR COMPONENTS:
 TRANSPARENT DUST COVER
 INSIDE MOLDING: LDPE
 STRAIN RELIEF: 45P PVC, BLACK
 OUTSIDE MOLDING: ABS, BLACK
 SHELL PLATING: GOLD FLASH
 CONTACT: GOLD PLATING
 CABLE: DP1.4
 [32AWG(7/0.08TC)+EAM]*5P+32AWG(7/0.08TC)*5C+AEB(16/7/0.12 85%AL)
 OD: 0.19 [4.8] COLOR: BLACK
 CABLE PRINTING: DISPLAYPORT CABLE E342987 AWM STYLE 20276 80°C 30V VW-1
- ELECTRICAL TESTING:
 100% OPEN & SHORT & CONTINUITY WIRE TEST
 CONTACT RESISTANCE: 2 OHM MAX.
 INSULATION RESISTANCE: 10M OHM MIN.
 HI-POT: 100V DC/10ms
- PACKAGING:
 ONE CABLE PER BAG




PIN ASSIGNMENT



P/N	LENGTH
BC-4D4D003F	36 [915]

THIRD ANGLE PROJECTION 		206 Van Vorst Street Jersey City, NJ 07302 +1 201 432 0463 http://www.belfuse.com
DO NOT SCALE DRAWING DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE	TITLE: DISPLAY PORT 1.4 CABLE, MALE TO MALE, 3 FEET	
DIMENSIONS: INCHES [METRIC]	THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.	DRN BY: JE DATE 10/07/20
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°		APPD BY: ADB DATE 10/20/20
SHEET NO. 1 OF 1		DWG NO. CT999225 REV. A0



ASSEMBLY FORMAT REV. 6/3/05

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[BC-4D4D003F](#)