



DATE	REV	ECN	APP'D. BY
5/29/19	A0	RELEASED	-
-	-	-	-




NOTES:

- CONNECTOR COMPONENTS:
 TRANSPARENT DUST COVER
 INSIDE MOLDING: PE
 OUTSIDE MOLDING: 45P PVC, BLACK
 SHELL PLATING: GOLD FLASH
 CONTACT: GOLD PLATING
 HIGH SPEED HDMI WITH ETHERNET CABLE: UL20276 [28AWG(7/0.127TC)*1PR +DW(1/0.32CCS)+AL/MYLAR]*5P+28AWG(1/0.32CCS)*3C+28AWG(7/0.127TC) +FILLER+AL/MY+DW(7/0.127TC)+BRAID(16/5/0.12AI/mg)+JACKET
 OD: 0.29±0.008 [7.3±0.2] COLOR: BLACK
 CABLE PRINTING: HIGH SPEED HDMI® CABLE WITH ETHERNET E342987 AWM STYLE 20276 80°C 30V VW-1 --- c AWM I/II A/B 80°C 30V FT1
- ELECTRICAL TESTING:
 100% OPEN & SHORT & CONTINUITY WIRE TEST
 CONTACT RESISTANCE: 5 OHM MAX.
 INSULATION RESISTANCE: 10M OHM MIN.
 HI-POT: 100V DC/10ms
- PACKAGING:
 ONE CABLE PER BAG




PIN ASSIGNMENT



P/N	LENGTH
BC-HH003F	36±0.8 [915±20]
BC-HH006F	72±1.2 [1830±30]
BC-HH010F	120±1.6 [3050±40]

ASSEMBLY FORMAT REV. 6/3/05



THIRD ANGLE PROJECTION 		206 Van Vorst Street Jersey City, NJ 07302 +1 201 432 0463 http://www.belfuse.com
DO NOT SCALE DRAWING DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE	TITLE: HDMI-A MALE TO HDMI-A MALE CABLE	
DIMENSIONS: INCHES [METRIC]	THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.	DRN BY: JMM DATE 05/16/19
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°		APPD BY: ADB DATE 05/29/19
SHEET NO. 1 OF 1		DWG NO. CT999189 REV. A0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[BC-HH003F](#) [BC-HH006F](#) [BC-HH010F](#)