

Coaxial Panel Connector 23_SMA-50-0-13/111_N

Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

| | |
|--------------------------|-------------|
| Impedance | 50 Ω |
| Interface frequency max. | 18 GHz |

Mechanical Data

| | |
|-------------------|-----------|
| Number of matings | 500 |
| Weight | 0.0023 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -65 °C to 125 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|-----------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Body | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Insulator | PFA / PTFE | |

Related Documents

| | |
|-------------------|--------------|
| Outline drawing | DOU-00174503 |
| Catalogue drawing | DCA-00010327 |

Ordering Information

| | |
|----------------------|-----------------------|
| Single package | 23_SMA-50-0-13/111_NE |
| Bulk 100 pcs package | 23_SMA-50-0-13/111_NH |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[23_SMA-50-0-13/111_NE](#)