





DC Power Plugs

171-3219-EX, 171-3220-EX



DC Power Plugs



Dimensions: (in.) mm

SPECIFICATIONS	
Color:	Black
Cap:	PP
Insulator A:	POM
Insulator B:	PC
Contact & Sleeve:	Nickel Plated Brass
Terminals:	Solder, Nickel Plated Brass
Insulation Resistance:	100MΩ (min.) @ 500VDC
Dielectric Strength:	500VAC for 1 minute
Voltage Ratings:	171-3219: 3.15V-6.3VDC
	171-3220: 6.3V-10.5VDC
Current Rating:	2A
Mating Jacks:	171-3219-EX: 163-4310-EX
	171-3220-EX: 163-4311-EX
RoHS Compliant by Exemption	

Date Last Revised: 10-26-07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-300910

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

171-3219-EX, 171-3220-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-3220-EX](#) [171-3219-EX](#)