

---

Item no.: 2010-1207  
Product description: 2-Conductor earth terminal block suitable for Ex e applications

---



Produkt kann von Bild abweichen / product may differ

Packing unit 25 pieces

RoHS compliant

Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Cross section [mm <sup>2</sup> ]	0.5 - 10 mm <sup>2</sup>
Cross section [AWG]	20 - 6 AWG
Connection method	CAGE CLAMP®S Connection
Cross section [mm <sup>2</sup> ]	0.5 - 16 mm <sup>2</sup>
Cross section [AWG]	20 - 6 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®S Connection
Nominal current (Ex e II)	51 A
Weight	28.321 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	37 mm
Height	1.46 in
Width	10 mm
Width	0.394 in
Depth	68 mm

Depth	2.68 in
Strip length from	17 mm
Strip length to	19 mm



Strip length	0.71 in
Customs Tariff No.	85369010
Country of Origin	Deutschland
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
2010-1207	ABS	05-HG476175/3-PDA			0,5-16
2010-1207	AEX	E185892			20-6
2010-1207	CCA	NL6011			0,5-10/16
2010-1207	CSA	154112-1645436			20-6
2010-1207	DNV	E-10423			0,5-6
2010-1207	GL	26187-05HH			0,5-10
2010-1207	KEMA	2095948.02			0,5-16
2010-1207	LR	91/20112(E6)			0,5-10
2010-1207	PRS	TE/1718/880590/08			0,5-16
2010-1207	PTB	IECEXPTB06.0003U			0,5-16
2010-1207	PTB	PTB05Atex1070U			0,5-16
2010-1207	RosTest	8189158			0,5-16
2010-1207	UR	E45172			20-6

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected