


# 2.5mm Right Angle 4 Conductor Cable **KOBI** **CONN**

172-7446-E

2.5mm Right Angle 4 Conductor Cable



**Dimensions: mm(in)**

CONNECTION	
P1	WIRE COLOR
1	BLUE
2	WHITE
3	GREEN
4	DRAIN

## ELECTRICAL SPECIFICATIONS

ITEM	SPECIFICATIONS
1	Operation Temperature: 0°C ~ + 70°C
2	Storage Temperature: -10°C ~ + 50°C
3	Temperature Cycle: 50°C/2 Hours. -10°C/2 Hours 3 Cycles.

## MATERIAL SPECIFICATIONS

ITEM	SPECIFICATIONS
1	Tensile Strength: Overmold to cable shall withstand 11LBS (5kgf) pull for one minute.
2	Bending Test Both SR.: Load Weight: 500g, Angle: Left: 90°, Right: 90°, Total: 180° Speed: 30 Cycles/Min. The cable must withstand 5000 cycles bending and not broken.
<b>RoHS Compliant</b>	

Date Last Revised: 03/12/12

Available from Mouser Electronics  
1-800-346-6873 / [www.mouser.com](http://www.mouser.com)

KC-301300

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

172-7446-E

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[172-7446-E](#)