

Fuse-link, high speed, 16 A, AC 690 V, 90 kA, BS88-4, 9 x 73 mm, aR, BS



Part no. **16A 690V AC BS88 SEMI**
 Catalog No. **16FC**

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	16
Rated voltage			AC 690 V
Construction size			BS88-4
Size			9 x 73 mm
Utilization category			aR
Breaking Capacity		kA	90
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-4 IEC 60269-4

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	16
Rated voltage		V	690
Voltage type			AC
Rated switching capacity		kA	90
Utilization category			aR (accompanied semiconductor protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusmann.com/pdf/4a317260-8e98-40d9-b43b-e80c53a102f6.pdf
-------------------------	---