

Model	NF-5330C
DC Voltage	0.1V~1000V± (0.5%+3)
AC Voltage	0.1V~750V± (0.5%+3)
DC Current	/
AC Current	/
Resistance	0.1Ω~60MΩ± (0.8%+3)
Capacitance	10pF~60mF± (3.5%+20)
Frequency	0.01Hz~8MHz ± (0.01%+3)
Duty Cycle	/
Display counts	6000 counts
Auto/Manual range	Auto
LCD Display	√/touch button
Live Test	√
NCV	√
Diode test	√
Continuity	√
MAXMINhold	MAX
Data Hold	√
True RMS	√
Battery test(1.5 V/9 V)	√
Low battery indication	√
AUTO power off	√
Double color backlight	√
Flashlight	√
Power	2x1.5V AA