



NOTES:

1. MATERIALS AND FINISHES:
 SMPM STR PLUG - BeCu, GOLD PLATING
 CABLE - 0.085 SEMI-RIGID CONFORMABLE
2. ELECTRICAL:
 A. IMPEDANCE: 50 OHM
3. PACKAGING:
 A. QUANTITY: SINGLE PACK
 B. MARKING: BAG TO BE MARKED
 "AMPHENOL RF, 95-725-111-XXX AND DATE CODE"

THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	20-Mar-17	3344	BMG
B	FREQUENCY AND VSWR REQUIREMENTS UPDATED	19-Mar-18	7383	BMG
C	UPDATED CONNECTOR DESIGN AND VSWR REQUIREMENTS	13-Jun-19	11841	EH



LENGTH TABLE		
PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH AND TOLERANCE 'L' IN INCHES [METERS]
95-725-111-030	-	3.00 [0.076]
-	95-725-111-M010	3.94 [0.100]
95-725-111-040	-	4.00 [0.102]
95-725-111-050	-	5.00 [0.127]
95-725-111-060	-	6.00 [0.152]
95-725-111-070	-	7.00 [0.178]
95-725-111-080	-	8.00 [0.203]
95-725-111-090	-	9.00 [0.229]
-	95-725-111-M025	9.84 [0.250]
95-725-111-100	-	10.00 [0.254]
95-725-111-110	-	11.00 [0.279]
95-725-111-120	-	12.00 [0.305]
95-725-111-180	-	18.00 [0.457]
-	95-725-111-M050	19.69 [0.500]
95-725-111-240	-	24.00 [0.610]
-	95-725-111-M075	29.53 [0.750]
95-725-111-360	-	36.00 [0.914]
-	95-725-111-M100	39.37 [1.000]
95-725-111-480	-	48.00 [1.219]
-	95-725-111-M200	78.74 [2.000]

TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

DESIGN REQUIREMENTS:	
<input checked="" type="checkbox"/> FREQUENCY : DC TO 18 GHz	<input checked="" type="checkbox"/> CONTINUITY
<input checked="" type="checkbox"/> VSWR : 1.30 MAX @ DC-10 GHz 1.50 MAX @ 10-18 GHz	<input checked="" type="checkbox"/> HI-POT : 500 VRMS
<input type="checkbox"/> INS. LOSS: ---- dB MAX	<input type="checkbox"/> OTHER

CUSTOMER OUTLINE DRAWING
 ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0.381 mm) ±.005 (0.127 mm) ± 1°	MATERIAL SEE NOTES	DRAWN ANANDH G	DATE 29-Sep-16	TITLE SMPM STR PLUG TO SMPM STR PLUG, USING 0.085 SEMI-RIGID CONFORMABLE CABLE, VARIOUS LENGTH	Amphenol RF www.amphenolrf.com
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE EAR # 7428	ENGINEER ANANDH G	DATE 29-Sep-16	SCALE: 4.0:1.0 SHEET 2 OF 2	DRAWING NO.95-725-111-XXX
	CONFIGURATION LEVEL: In Work	APPROVED K. CAPOZZI	DATE 13-Jun-19	DWG SIZE B	ITEM NO.95-725-111-XXX
	FINISH	CAD FILE		REV C	PART NO.95-725-111-XXX