

# TORQUE WRENCH PLUS 3/8 INCH DR 100NM

Item ID: 3892P100



- 3/8" drive torque wrench covering 20-100Nm
- Click type mechanism with easily recognisable signal when the required torque is reached
- Simple to adjust and easy to read Nm scale
- Locking button to ensure the set torque is securely maintained to avoid errors
- Compact head for easier use in confined spaces
- Quick release 72 teeth ratchet mechanism with twist reverse conforms to DIN3122
- Designed to torque right hand (clockwise) fasteners
- Ergonomic bi-material grip for added comfort
- Clearly marked with a red band to show the correct place on the handle where pressure should be applied to give a more accurate torque reading
- Hanging facility which can be used together with a safety wire for added security when working at heights
- Accurate to +/- 4% and conforms to ISO6789 for assured reliability and accuracy
- Individually tested and certified at the time of manufacture
- Each torque wrench has it's own individual certification number for easier quality control management
- Supplied in a handy storage case

Length (mm): 90

Width (mm): 560

Height (mm): 70

Weight (kg): 1.705

*Technical changes and errors may occur*

**WWW.TENGTTOOLS.COM**



*Get organised™*