



TOP LEVEL NUMBER	SKU NUMBER	TYPE	DM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PRODUCT SPEC
87-6001-221	98-0003-2788-6	SER	8.00"	AG500	33284
87-6001-231	98-0003-2789-4	AMP	8.00"	AG500	33284

OGA DIAGONAL: 20.44 [519.08]
 VA DIAGONAL: 19.83 [503.63]
 PA DIAGONAL: 18.72 [475.43]

KAPTON TAPE



PINOUT	
1	UL
2	UR
3	SHLD
4	LR
5	LL

- NOTES:
1. WEIGHT OF GLASS IN GRAMS: 2340 ±10%.
 2. DIMENSIONS AND TOLERANCES DO NOT APPLY TO AREA 15 MM AROUND HARNESS EXIT.
 3. LATCH STYLE HOUSING P/N: 104257-4
 4. TIN CONTACTS P/N: 1-104480-7

UNITS: INCHES [MM]

TOLERANCES UNLESS OTHERWISE SPECIFIED

.XX ±.03 [7.6]

.XXX ±.015 [3.8]

ANGLES ±Z

3M TOUCH SYSTEMS
METHUEN, MA
USA

© 2007 3M. ALL RIGHTS RESERVED. REPRODUCTION OF THIS DOCUMENT WITHOUT THE WRITTEN PERMISSION OR USED FOR PURPOSES OTHER THAN THAT AUTHORIZED IS PROHIBITED.

DATE: 3/13/07

SCALE: 1 = 1

REV	DATE	BY	CHKD	DESCRIPTION
03	5/09	SEB		REVISED PER CO 030448
02	6/08	SEB		REVISED PER CO 029071
01	3/07	MTD		INITIAL RELEASE PER CO 027129

MARKETING DRAWING
 SCT76NN 19.83"

DO NOT SCALE DRAWING

DATE: 3/13/07

SCALE: 1 = 1

33589-MKT

1 OF 1

03