

Industrial PC - BL2 BPC 1501E - 1130669

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



IP30-rated fanless industrial box PC (BPC) with energy-efficient Intel® Celeron® N3350 processor, 32 GB eMMC mass storage, open M.2 slot, and 2x COM ports



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	900.000 g
Country of origin	Taiwan

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Computer data

Processor	Intel® Celeron® N3350 1.10/2.40 GHz
Cooling	passive
RAM	4 GB LPDDR4
Mass storage	32 GB eMMC internal
Interfaces	1x DP++
	2x USB 3.0
	2x COM ports

General

Mounting	Din rail mount included, optional wall mount kit (1147655) must be ordered as an accessory
Mounting type	DIN rail mounting
Weight	0.697 kg

Industrial PC - BL2 BPC 1501E - 1130669

Technical data

Ambient conditions

Degree of protection	IP30
	IP30
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Vibration (operation)	1g, according to EN 60068-2-6
Shock	15g, 11 ms in accordance with IEC 60068-2-27

Dimensions

Outer dimensions: width, height, depth	99 mm x 92 mm x 63 mm
--	-----------------------

Device supply

Supply voltage range	12 V DC ... 30 V DC
Typical current consumption	0.53 A (24 V DC)
Battery type	BR2032

Standards and Regulations

Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6
Conformance	CE-compliant
FCC	Title 47 Part 15 Subpart B:2018 Class A

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Classifications

eCl@ss

eCl@ss 10.0.1	19200102
eCl@ss 11.0	19200102
eCl@ss 4.0	27250315
eCl@ss 4.1	27250315
eCl@ss 5.0	27259205
eCl@ss 5.1	27242401
eCl@ss 6.0	19200100
eCl@ss 7.0	19200102
eCl@ss 9.0	19200102

ETIM

ETIM 4.0	EC001413
----------	----------

Industrial PC - BL2 BPC 1501E - 1130669

Classifications

ETIM

ETIM 6.0	EC001413
ETIM 7.0	EC001413

Approvals

Approvals

Approvals

EAC-RoHS / EAC / UL Listed / IECEE CB Scheme / cUL Listed / cULus Listed

Ex Approvals

Approval details

EAC-RoHS			RU*- DE*HB.B.00386/20
----------	--	--	--------------------------

EAC			RU C- DE.A*08.B01708
-----	--	--	-------------------------

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
-----------	--	---	---------------

IECEE CB Scheme		http://www.iecee.org/	US-36577-UL
-----------------	--	---	-------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
------------	--	---	---------------

cULus Listed			
--------------	--	--	--

Industrial PC - BL2 BPC 1501E - 1130669

Accessories

Accessories

Adapter cable

Adapter - DP TO VGA ADPTR - 2400173

DisplayPort to VGA video adapter



Adapter - DP TO DVI ADPTR - 2400174

DisplayPort to DVI-i video adapter



Battery (not rechargeable)

Battery / accumulator - BL2 BPC 1500 RTC BATTERY - 1147739

Replacement battery (BR2030) for BL2 BPC 1500... IPCs



Data front plate

Data interface - SI-SES-U1A/0,6 - 1404514

Service socket with USB (socket/plug), type A with 0.6 m cable



Mounting material

Industrial PC - BL2 BPC 1501E - 1130669

Accessories

Mounting kit - BL2 BPC 1500 WALL MOUNT KIT - 1147655



Mounting kit

Mounting kit - BL2 BPC 1500 DIN RAIL KIT - 1147464



DIN rail mounting kit for BL2 BPC 15... products

Programming cable

Connecting cable - VL 2.0M DP CABLE - 2404774



DisplayPort (DP) cable (2 m) for use with industrial computers

Storage medium

Memory - BL2 BPC 1500 64GB M.2 SSD KIT - 1147738



64 GB M.2 SSD kit for BL2 1500 IPC, heat spreader, bracket, and thermal pads are included

Memory - BL2 BPC 1500 128GB M.2 SSD KIT - 1147737



128 GB M.2 SSD kit for BL2 1500 IPC, heat spreader, bracket, and thermal pads are included

Industrial PC - BL2 BPC 1501E - 1130669

Accessories

Spare parts

Printed-circuit board connector - MC 1,5/ 2-STF-3,5 - 1847055



PCB connector, nominal cross section: 1.5 mm², color: green, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Tin, type of contact: Female connector, Number of potentials: 2, Number of rows: 1, Number of positions per row: 2, number of connections: 2, product range: MC 1,5/..-STF, pitch: 3.5 mm, connection method: Screw connection with tension sleeve, conductor/PCB connection direction: 0 °, plug-in system: MINI COMBICON, Locking: Screw locking, type of packaging: packed in cardboard
