



# Qoltec Patchcord fiber optic LC/UPC - LC/UPC | Multimode | 50/125 | OM4 | Duplex | 5m

Product code: 54346

Patchcord fiber optic multimode  
Connectors: LC/UPC - LC/UPC  
Standard: OM4  
Diameter cable: 3.0 mm  
Cable length: 5 m

Technical data

Type connectors	LC/UPC - LC/UPC
Type patchcord	Multimode
Type of fiber optic transmission	Duplex
Standard fiber	OM4
Fiber type	50/125
Sheath	LSZH
Diameter cable	3.0 mm
Cable length	5 m
Reinforcing element	Aramid fiber
Colour	Pink
Additional information	Easy installation and handling on high speed fiber optical transmission networks. LSZH - Outside fireproof cable sheath, which the fire does not emit harmful gases. The product individually tested.
Package	Polybag
Net weight	0,066 kg
Gross weight	0,077 kg
Producer	Qoltec
EAN code	5901878543468

	100 Mb Ethernet	1 Gb Ethernet	10 Gb Ethernet	40 Gb Ethernet	100 Gb Ethernet
OM2 (50/125)	2km	550m	82m	Nie wspiera	Nie wspiera
OM3 (50/125)	2km	800m	300m	100m	100m
OM4 (50/125)	2km	1100m	550m	125m	125m