


Model 1658
Cable Assembly Type "N" Male Both Ends



MATERIALS:

Conn: 1st end – Type "N" Male, See table above.

Finish: Body and Fitting, Tarnish resistant.

Center contact: Gold plated per requirement of MIL-C-39012.

Nominal Impedance: 50 Ohms.

Cable: See table above. Marking: "POMONA 1658-T-XX".

Conn: 2nd end – Same as first end.

RATINGS:

Operating Voltage: 1000 VRMS Max.

Operating Temperature: +89°C Max.

ORDERING INFORMATION: Model 1658-T-XX

XX = Cable Lengths, Standard Length: 18" (457), 24" (610), 36" (914), 48" (1219) & 60" (1542).

Additional lengths can be quoted upon request.

Ordering Example: 1658-T-24 Indicates 24" in length

Cable	
	RG214/U (Double Shield)
Model	1658-T-XX
Capacitance pf/ft	30.8
Nominal Impedance	50
Cable Diameter	$\phi .425$

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1658-T-18](#) [1658-T-60](#) [1658-T-48](#) [1658-T-36](#) [1658-T-24](#)