


# Pinch valve

## VZQA-C-M22U-15-GG-ALPOMN-4

Part number: 3022832

FESTO



### Data sheet

Feature	Value
Design structure	Pneumatically actuated pinch valve
Type of actuation	pneumatic
Sealing principle	soft
Assembly position	Any
Mounting type	Line installation
Process valve connection	G1/2
Nominal diameter DN	15
Valve function	2/2 open, monostable
Flow direction	reversible
Medium pressure	0 ... 4 bar
Operating pressure	1 ... 6.5 bar
Nominal pressure of process valve	10
Differential pressure	2.5 bar
Bursting pressure	16 bar
Overload pressure	7.8 bar
Type of reset	Rebound resilience
Type of piloting	With external control
Auxiliary pilot air port 12	G1/8
Pilot medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Medium	Compressed air in accordance with ISO8573-1:2010 [-:-:-]
Max. viscosity	4,000 mm <sup>2</sup> /s
Medium temperature	-5 ... 60 °C
Ambient temperature	-5 ... 60 °C
Storage temperature	6 ... 8 °C
Flow rate Kv	5 m <sup>3</sup> /h
Switching time on	250 ms
Switching time off	250 ms
Materials note	Contains PWIS substances Conforms to RoHS
Material housing	Wrought Aluminium alloy
Material housing cover	POM
Material seals	FPM
Material shut-off element	NBR
Product weight	158 g
Material bowl	PA6