
THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




BACKSHELL KIT INCLUDES:

(2)BACKSHELL HALVES
(2)4-40 THUMBSCREWS
(2)HOUSING SCREWS & (2)NUTS
(1)SET OF COMPRESSION INSERTS-VARIOUS SIZES DIAMETERS:4mm(.157"),5mm(.197"),7mm(.276"),9mm(.351")

NOTE: 37 POSITION HAS (4) HOUSING SCREWS & (4)NUTS





* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS:

DIMENSIONS(mm/in)				
SIZE	A +1.30(+.051) 50(02)	B ±.50 ±.02	C ±1.60 ±.063	D +1.30(+.051) 30(012)
9	31.20	24.99	39.90	15.00
	1.228	0.984	1.571	0.591
	39.50	33.32	41.50	15.00
15	1.555	1.312	1.634	0.591
25	53.40	47.04	48.60	15.00
	2.102	1.852	1.913	0.591
37	69.70	63.50	53.60	15.00
	2.744	2.500	2.110	0.591

ORDERING INFORMATON:

THESE DRAWINGS AND SPECIFICATIONS ARE THE

WRITTEN PERMISSION.

PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT

BE REPRODUCED. COPIED OR USED AS THE BASIS FOR

THE MANUFACTURE OR SALE OF APPARATUS WITHOUT

MH CONNECTORS LTD.

-			
	SIZE	P/N – KITTED	PRODUCT CODE
	9-WAY	6560-0108-01	MHDTPPK-9-K
	15-WAY	6560-0108-02	MHDTPPK-15-K
	25-WAY	6560-0108-03	MHDTPPK-25-K
	37-WAY	6560-0108-04	MHDTPPK-37-K

SIZE	P/N – BULK	PRODUCT CODE
9-WAY	6561-0108-01	MHDTPPK-9
15-WAY	6561-0108-02	MHDTPPK-15
25-WAY	6561-0108-03	MHDTPPK-25
37-WAY	6561-0108-04	MHDTPPK-37

DRAWN

SCALE

JOHNNY

VICTOR

DRAWING No

MHDTPPK SERIES

APPROVED

DATE

DATE

SHEET OF

1 DF 1

11-02-15

11-02-15

REV:

2.0

PLASTIC: ABS UL 94-HB RATED JACKSCREWS: STEEL-BLACK OXIDE FINISH M3 HOODSCREWS: STEEL-BLACK OXIDE FINISH COMPRESSION INSERTS: ABS UL 94-HB RATED M3 NUTS: STEEL-BLACK OXIDE FINISH OPERATING TEMP: -55°C TO+110°C



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.





COMPLIANT	SHEE
⊳	m <u>⊣</u>

AND 2002/96/EC FOR RoHS COMPLIANCY.	THIS SERIES FULLY CONFORMS TO THE
-------------------------------------	-----------------------------------

CONNECTORS

MHDB37SP	MHDB25SP	MHDB15SP	MHDB9SP	PN
37	25	15	60	PIN
69.50	53.03	39.25	30.81	A
63.50	47.04	33.32	24.99	в
55.42	38.96	25.25	16.92	С
57.40	41.30	27.75	19.28	D





Ø3, 140, 2



THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.


* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS: ANGLE ± 1° .X ± 0.15 .XX ± 0.05

Remark:

1.SPECIFICATION: Rated voltage:250V Rates current:5AMP Withstand voltage:500V Per mintute Contact resistance:20MΩ MAX Insulation resistance:1000MΩ MIN.at 500V DC Temperature range:-55 -105°C

2.MATERIAL

Spcc shell:Spcc front shell is ni plated back shell is tin plated Plastic:PBT+30% G.F (UL94V-0) BLACK Terminal:brass ,tin-gold plated



Œ

Œ

④ D±0.25

С

 \square

l

MH CONNECTORS LTD.	BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT
1:1 DRAWING No MHDB SP	APPROVED	DRAWN Johnny
1 OF 1		
	DATE	DATE 07-16-12
		5-12