

TG24

24 Hour Compact Plug-In Segment Time Controller

Features & Benefits

- 24 hour compact plug in timer.
- 15 minute minimum switching interval which can be increased in 15 minute steps.
- Permanent ON override for instant control.
- Easy to use segment setting dial.



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Plug-in
Earth Class Rating	Class I
Operating Temperature	0°C to 40°C
Ingress Protection Rating	IP20
Setting Type	Segment
Program Modes	24 Hour, Perminant ON/OFF or Timed
Socket Outlet	Single Gang UK Plug Socket
Switch type	Single Pole
Standby Consumption	<1W

Data sheet

TG24

Time / Time Controllers

Switch rating	13A Resistive, 2A Inductive, 60W LED, 400W Halogen, 100W CFL
Programmable Slots	48 ON 48 OFF (96 Segments)
Permanent ON Facility	Yes (Slider Switch)

General

Weight (g)	123
Height (mm)	76
Width (mm)	79
Depth (mm)	67.5
Body Construction	Polycarbonate
Product Colour	White
EAN Number	5012483009970
Guarantee Period	3 Years

Line Diagrams

