



Pigtail fiber optic LC/APC | Singlemode | 9/125 | G652D | 1m

Product code: 54099

Pigtail fiber optic singlemode
Connectors: LC/APC
Standard: G652D
Diameter cable: 0.9 mm
Cable length: 1 m

Technical data

Type connectors	LC/APC
Type pigtail	Singlemode
Standard fiber	G652D
Fiber core diameter	9/125 m
Sheath	LSZH
Diameter cable	0.9 mm
Insertion loss	<0.3 dB
Return loss	>60 dB
Cable length	1 m
Colour	White
Additional information	Easy installation and handling on high speed fiber optical transmission networks. LSZH - Outside fireproof cable sheath, which the fire does not emit harmful gases. The product individually tested.
Package	Polybag
Gross weight	0,006 kg
EAN code	5901878540993