




2427S

ERGO™ 45° Bent Tip Snipe Nose Pliers with Insulated Dual-Component Handles and Phosphate Finish



PRODUCT DETAILS

- Two-component ERGO™ insulated handles: thermoplastic surface on tough polypropylene base provides superior grip
- Developed according to the scientific ERGO™ process
- For working on live equipment up to 1000 V in compliance with IEC 60900
- Cutting capacity: 2.5 mm to 3 mm copper, 1.8 mm iron, 1.4 mm to 1.6 mm iron alloy
- Half-round serrated jaws for gripping flat and round material with great accessibility in confined spaces
- Bent jaws with hardened cutting edges for cutting soft and hard wire
- High-performance alloy steel
- Phosphate finish, anti-corrosion treated
- Standards: ISO 5745, IEC 60900
- Every tool is tested at 10,000 V for 10 seconds at the end of the manufacturing process







Follow the Fish!







PRODUCT ATTRIBUTES

Product: **2427S-160**

A	160 mm	B	46 mm	C	16,5 mm
D	8,9 mm	E	3 mm	F	2,5 mm
G	12 mm	 3.0 mm	 1.8 mm		
	1.6 mm		160 g		

Product: **2427 S-200**

A	200 mm	B	65 mm	C	17 mm
D	9,4 mm	E	3 mm	F	2,5 mm
G	12 mm	 3.0 mm	 1.8 mm		
	1.6 mm		170 g		

