



Deep groove ball bearings, single row, seal on both sides

| Principal dimensions | | | Basic load ratings | | Fatigue load limit P_u | Speed ratings | | Mass | Designation |
|----------------------|----|---|--------------------|--------|-----------------------------|-----------------|----------------|-------|-------------|
| d | D | B | dynamic | static | | Reference speed | Limiting speed | | |
| mm | | | kN | | kN | r/min | | kg | - |
| 8 | 22 | 7 | 3,45 | 1,37 | 0,057 | - | 22000 | 0,012 | 608-2RSH * |



Calculation factors

$k_r = 0,025$
 $f_0 = 12$