

# FCxx\*1)S0G1-4476

e.g. FC25S0G1-4476


\*1) xx No. of contacts 09, 15, 25 or 37

RoHS compliant

xx	A [mm]	B [mm]	C [mm]
09	30.8	16.4	25
15	39.1	24.7	33.3
25	53	38.5	47.04
37	69.3	54.9	63.5

## Packing unit on supplement AM0409.

4	xx	Signal contact	S36 / Brass / AWG 20	0.3µm Au / C-Filter 1nF -20/+80%
3	1	Shell	Steel	tin plated
2	1	Sealing compound	Epoxy resin (-55°C - +85°C)	black
1	1	Insulator	Plastic	black
No.	St.	Type Description/Material		
<small>Measurement without tolerances to</small> <small>ISO 2768-m</small> <small>SCALE 2:1</small> <small>TITLE</small> <small>NAME / DATE</small> <small>08-04-2016</small> <small>DRAWN</small> <small>08-04-2016</small> <small>CHECKED</small> <small>08-04-2016</small> <small>sschref</small>				

D-Sub Filter-Connector		DWG.NO.	FCxxS0G1-4476	REV.	1
TITLE		REPLACEMENT FOR:	ORIGINAL DN A3-DRAWING AS A FILE	PAGES	1
SCALE		 <small>a moflex company</small>			
DATE		CH.-NO.	<small>REPLACEMENT FOR:</small> <small>ORIGINAL DN A3-DRAWING AS A FILE</small>		

COMMENT:  
 ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING, WITHOUT OUR PRIOR CONSENT,  
 IT MAY NEITHER BE PUBLISHED NOR MADE AVAILABLE TO A THIRD PARTY,  
 AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.