Manual Tensioning Tool for KR-Series

KR6/8

Application tool KR6/8 crimps the glass-fibre-reinforced locking pin of the KR seal and leads to plastic deformation of the tie ends. This produces a very permanent connection.

Features and Benefits

- · Tough metal tool
- For applying KR-cable ties only
- · For tensioning, fixing and cutting KR-cable ties
- Simply change the front plate to apply two different strap widths: 6 mm and 8 mm



KR6/8.

ТҮРЕ	For Ties	Strap Width max. (G)	Weight	Article-No.
KR6/8	KR6, KR8	8.0	0.52 kg	121-00680
SP KR6/8 replacement blade	KR6, KR8	-	0.01 kg	122-68019

All dimensions in mm. Subject to technical changes.

Pneumatic Tensioning Tool for KR-Series

KR8PNSE

Application tool KR8PNSE crimps the glass-fibre-reinforced locking pin of the KR seal and leads to plastic deformation of the tie ends. This produces a very permanent connection.

Features and Benefits

- · Tough metal tool
- Pneumatic
- For applying KR-cable ties only
- For tensioning, fixing and automatically cutting KR-cable ties
- Tensioning force can be adapted with the air pressure
- Holding ring for a balancer



KR8PNSE.

Air Supply	Non oiled / oiled	
Air Pressure (min.)	3 Bar	
Air Pressure (max.)	4 Bar	
Hose Internal Diameter	6.0 mm	
LxHxW	approx. 320 x 210 x 50 mm	
Specifications	CE, GS	



ТҮРЕ	For Ties	Strap Width max. (G)	Weight	Article-No.
KR8PNSE	KR8	8.0	1.56 kg	121-00889
SP KR8PNSE replacement blade	KR8	-	0.01 kg	122-80032

All dimensions in mm. Subject to technical changes.



For product specific approvals and specifications please refer to the Appendix.

