


24 2411 07

# USB and IEEE 1394 connectors



USB 2.0 chassis socket type B, angular version, for printed circuit boards


1 of 3 05/2020



# Temperature range La. 50±a.20 Materials Insulating body

Insulating body
PBT, V-0 according to UL94
Contact spring
CuZn, gold-plated in mating area, tin-plated in solder area
Housing
CuZn/steel, nickel-plated

-40 °C/+85 °C




### Mechanical data

Insertion force  $\leq 35 \text{ N}$  Withdrawal force  $\geq 10 \text{ N}$ 

### Electrical data (at Tamb 20 °C)

Contact resistance ≤ 30 mΩ Rated current 1.5 A Rated voltage 30 V DC Rated impulse voltage 500 V AC Insulation resistance ≥ 1 GΩ



## Associated products

Counterparts

☐ 2431

Accessories 2412 02

\*a printed circuit board layout

2 of 3



24 2411 07

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
2411 07	4	100	500

### Packaging:

in a tray

3 of 3 05/2020