

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet

tasker® T42 PVC – 7x0.40/4.80/7.10

12G-SDI Coaxial Video Cable 75 Ω



CATEGORY Coaxial cable 75 Ω (See Video Catalogue)
APPLICATIONS Digital video for broadcast and high definition video installation

- A:** Extra Flex **PVC** Sheath. Available in different colors.
Outer Diam. Ø 7,10 (±0,20) mm.
- B:** First Shielding O.F.C. tinned copper Braid covering 89%
- C:** Second Shielding O.F.C. tinned copper Braid covering 86%.
- D:** Core Insulation with Gas Inject Foam PE. Diam. Ø 4,80 (±0,20) mm.
- E:** O.F.C. Red Copper stranded formation 7x0,40 mm.
Nom. Cross section 1x0,88 mm².

MARKING **tasker®** T42 PVC – 1x0,88 mm² (75Ω) – O.F.C. - GAS INJECTED FHDPE – EXTRA-FLEX PVC SHEATH COAX VIDEO HDTV/SDI CABLE -
- Made in Italy

CUSTOM PRODUCTION This product may be custom produced also in **L.S.Z.H.** polymer, **PE, PUR**, with or without Metallic Armor.

Cable Properties

Conductor Resistance	21 Ω/Km
Capacity Core/Shield	53,0 pF/m
Velocity of Propagation	86%
Impedance	75 Ω
Nom. Delay	4,1 ns/m
HD-SDI Max Distance	100 m
Operative Temperature	-15/+70°C

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Attenuation dB/100 m.

10 MHz	2,03
100 MHz	6,71
1000 MHz	22,5
2000 MHz	33,98
3000 MHz	44,96
4500 MHz	52,79
6000 MHz	70,01

recommended installation distances

HD-SDI	120
3G-SDI	100
6G-SDI	70
12G-SDI	70

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS3 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. B / 07.01.19
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			