

**L (мм)**

<b>ТС-0112</b>	4,3
<b>ТС-0113</b>	5,0
<b>ТС-0114</b>	7,0
<b>ТС-0115</b>	7,3
<b>ТС-0116</b>	8,0
<b>ТС-0117</b>	8,5
<b>ТС-0118</b>	9,5
<b>ТС-0119</b>	12,5

**Параметры:** DC 12В 50мА**Ход:**  $0,25 \pm 0,1$ мм**Сопротивление контактов:** 100 мОм макс.

<b>Код</b>	<b>Сила нажатия (г)</b>	<b>Ресурс (циклов)</b>
<b>T</b>	$100 \pm 30$	$>= 500000$
<b>V</b>	$130 \pm 30$	$>= 500000$
<b>X</b>	$160 \pm 50$	$>= 300000$
<b>W</b>	$170 \pm 50$	$>= 300000$
<b>Y</b>	$190 \pm 50$	$>= 150000$
<b>Z</b>	$250 \pm 100$	$>= 100000$

