

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008500008](#)
Status: **Active**
Overview:
Description: KK 396 Crimp Terminal 8818, 18-22 AWG, Reel, Brass Tin (Sn)

General

Product Family	Crimp Terminals
Series	8818
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	kk_interconnect_solutions
Packaging Alternative	08500023 (Loose)
Product Name	KK 396
UPC	800753617889

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.180/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.41mm max.
Wire Size AWG	18, 20, 22
Wire Size mm ²	N/A

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	8818-(P909)
--------------------	-------------

Reference - Drawing Numbers

Packaging Specification	PK-2759-002-001
Product Specification	PS-08-50-001
Sales Drawing	SD-8818-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[8818](#) Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Hand Crimp Tool for	638280300
3.96mm Pitch KK	
Crimp Terminals,	
18-22 AWG	
Mini-Mac Applicator	638881100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[08-50-0008](#)