

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [90059-0009](#)
Status: **Active**
Overview: C-Grid III™
Description: 2.54mm Pitch C-Grid® Micro Shunt, Low Profile, 0.381µm Select Gold (Au) with Gold (Au) Flash Plating

Documents:

[3D Model](#) [Product Specification PS-90059 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Accessories
 Series [90059](#)
 Component Type Shunt
 Overview [C-Grid III™](#)
 Product Name C-Grid®, C-Grid III™, SL™
 UPC 800753539143

Physical

Circuits (Loaded) 2
 Color - Resin Natural
 Flammability 94V-0
 Gender Female
 Lock to Mating Part None
 Material - Metal Phosphor Bronze
 Material - Plating Mating Gold
 Material - Plating Termination Nickel
 Material - Resin Polyester
 Net Weight 70.025/mg
 Number of Rows 1
 Packaging Type Bag
 Plating min - Mating 0.381µm
 Plating min - Termination 0.203µm
 Temperature Range - Operating -55°C to +125°C
 Termination Interface: Style Surface Mount


Electrical

Current - Maximum per Contact 3A

Material Info

Reference - Drawing Numbers

Product Specification PS-90059
 Sales Drawing SDA-90059



EU RoHS

**ELV and RoHS
 Compliant**
**REACH SVHC
 Contains SVHC: No
 Low-Halogen Status
 Not Low-Halogen**

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[90059Series](#)

Use With

(0.64)/.025 square and round pins