


Product sheet Subminigture connectors

Product Female cable connector, moulded, shieldable Pole 2
Area M9 connectors IP 67 serie 702 Article number 79 1402 12 02

illustration





Contact Arrangement

0

1 weiß 2 braun

Installation instructions / Mounting cutout



Technical data

Common values

Connector Design Female cable connector Connector locking system Screw-locking

Termination moulded on cable

Wire gauge (mm) 0,25 mm²

Wire gauge (AWG) 24

Max. Cable outlet Upper temperature +70 °C

Lower temperature -25 °C

Electrical values

125 V Rated voltage 1500 V Rated impulse voltage 1 Pollution degree Ш Overvoltage category Ш Material group Rated current (40°C) 4 A ≤ 3 mΩ Volume resistivity shielded EMV compliance IP 67 Degree of protection >500 mating cycles Mechanical operation

Material

Material of contact CuSn (bronce)
Contact plating Au (gold)
Material of contact body PBT (UL 94 V-0)
Material of housing PUR

Cable data

material housing PUR insulation single lead PVC single lead structure $14 \times 0,15 \text{ mm}$ cable sheath Ø 5.3 conductor resistance $75\Omega/\text{Km}$ bending radius cable fixed Min. 53 mm bending radius cable movable Min. 80 mm cable diameter 5.3 mm

Contacts 2, Female cable connector, moulded, shielded, Cable length 2 m

