

General Tolerance unless stated $\pm 0.3\text{mm}$

The individual **product features** are displayed at the foot of the table...

REF. NO.	Fixing Holes	Ball Size (mm)	Weight in (Kgs)	Support Load (Kgs)			
				TYPE 13 Carbon Steel Bearings, Zinc Plated Pressings		TYPE 15 Stainless Steel Bearings and Pressings	
				Load Up	Load Down	Load Up	Load Down
3016	2	15.8					
3000	2	19	0.087	25	10	25	10
3006	3						
3025	2	25	0.135				
1000	2	25	0.175	55	25	55	25
1008	3						
1022	3						
1035	2	32	0.265	125	55	125	55
2000	2	40	0.515	140	60	140	60
2011	3						
4001	3	50	1.065	340	100	250	100
1502	2	25	0.196	100	50	100	50
1010	-	25	0.195	55	25	55	25
1030	-	32	0.275	125	55	125	55
2002	3	40	0.635	225	100	225	100

To order, specify REF No and TYPE, i.e. 3016-13


3016-4001



Features: General purpose. Low profile, dirt hole. No seals in 3016 and 3025 units.


Also available with a solid steel inner ring (SI) option without seal.

1010/1030




Features: Press ball unit into hole to fix, prise out to remove. Units can either be fixed or replaced quickly. Low profile, dirt exit hole.

1502



Features: Low profile, high load capacity. Knife edge seal on load ball. Dirt exit hole. Requires 5mm radius on fixing hole.

2002 XTRA - TUF



Features: Heavy duty construction, designed for arduous and dirty conditions. Flushing hole for cleaning, extra large dirt exit hole.

3 Holes for heavy duty cleaning.