

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1122190041](#)
Status: **Active**
Overview: [Woodhead ArcArrest Connector System](#)
Description: Woodhead ArcArrest Receptacle with Handle, Switch-Rated, 30.0A, 600V AC, 3-Pole +Ground, Insulator Keying Position 14, Three Grommets Included

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

UL E145922

General

Product Family Wiring Devices
 Series [112219](#)
 IP Rating IP69K
 NEMA Configuration N/A
 Overview [Woodhead ArcArrest Connector System](#)
 Product Name ArcArrest
 Receptacle Type Single
 Specialty Switch-Rated
 Type Receptacle
 UPC 78172558754
 Wire Size AWG 8 to 12

Physical

Cord Grip Body Size F4 1"
 Flange Yes
 Flip Lid Yes
 Gender Female
 Length 199.08mm (7.838")
 Locking Blade N/A
 Net Weight 98.540/g
 Poles 3

Electrical


Cord Type N/A
 Current - Maximum per Contact 30.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 600V AC

Material Info

Engineering Number ARC30FHF03

Reference - Drawing Numbers

Sales Drawing 1122190038-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[112219 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1122190041](#)