

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300390300](#)  
**Status:** **Active**  
**Overview:**  
**Description:** DeviceNet Trunk Receptacle, 5 Poles, 1/2" - 14 NPT, Male (Straight) to Leads, 2.0m (6.56') Length

**Agency Certification**

CSA	LR6837
UL	E152210

**General**

Product Family	Industrial Receptacles
Series	<a href="#">130039</a>
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	minichange_products
Product Name	DeviceNet Trunk
Type	Single Ended (pigtail)
UPC	78678829667

**Physical**

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	2.0m
Material - Component	Gray Anodized Aluminum
Mounting Thread Size	1/2" - 14 NPT
Net Weight	21.000/g
Orientation	Straight
Panel Mount	Front
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire Size AWG	15, 18
Wire/Cable Type	Thick Standard Cable

**Electrical**

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V AC/DC

**Material Info**

Engineering Number	DN5100-M020
--------------------	-------------

**Reference - Drawing Numbers**

Sales Drawing	SD-130039-001-001
---------------	-------------------

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c),6(b)**

**REACH SVHC**

Not Contained Per - ED/108/2014 (17 Dec 2014)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[130039](#) Series

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300390300](#)