

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200668995](#)
Status: **Active**
Overview: Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Description: Micro-Change (M12) Double-Ended Cordset with Knurled Hexnut, 5 Poles, Female (Straight) to Male (Straight), 22 AWG, Unshielded WSOR Cable, Grey 5th Wire, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
 Series [120066](#)
 Connector End A Micro-Change (M12)
 Connector End B Micro-Change (M12)
 IP Rating IP67
 Material - Contact Brass
 Overview [Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable](#)
 Product Name Micro-Change (M12)
 Region Europe
 Type Double Ended
 UPC 889056071086

Physical

Cable Diameter 5.50mm (.216")
 Cable Length 5.0m (16.40')
 Color - Cable Jacket Black
 Coupling Style Knurled Hexnut, Threaded
 Gender Female-Male
 Keyway Single
 LED Indicator No
 Material - Cable Jacket TPU
 Material - Connector Body TPU
 Material - Coupling Nut Nickel-plated Brass
 Material - Plating Mating Gold
 Orientation Straight to Straight
 Poles 5
 Temperature Range - Operating -25°C to +85°C
 Wire Size AWG 22
 Wire/Cable Type WSOR

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 60V

Material Info

Engineering Number 885030B30M050

Reference - Drawing Numbers

Sales Drawing 1200659548-00P, 1200668993-000



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120066](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION