

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200680195](#)  
**Status:** **Active**  
**Overview:** Brad Micro-Change (M12) Connectors  
**Description:** Micro-Change (M12) In-Line Splitter, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), Y-Splitter with LEDs

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E152210

**General**

Product Family Industrial Tees and Splitters  
 Series [120068](#)  
 IP Rating IP67  
 Overview [Brad Micro-Change \(M12\) Connectors](#)  
 Product Name Micro-Change (M12)  
 Type Splitter - In-line  
 UPC 78678882747

**Physical**

Color - Cable Jacket Yellow  
 Drop Connector N/A  
 Drop Gender N/A  
 Keyway Single  
 LED Indicator No  
 Left Trunk Connector Micro-Change (M12)  
 Left Trunk Gender Male  
 Leg 1 Length 0.30m  
 Leg 2 Length 0.30m  
 Material - Cable Jacket TPE  
 Material - Connector Body TPE  
 Material - Coupling Nut Nickel-plated Brass  
 Net Weight 107.672/g  
 Poles 3 Female/4 Male  
 Right Trunk Connector Micro-Change (M12)  
 Right Trunk Gender Female  
 Temperature Range - Operating -30°C to +70°C

**Electrical**


Current - Maximum per Contact 4.0A  
 Voltage - Maximum 250V AC/DC

**Material Info**

Engineering Number 884A30K05M003

**Reference - Drawing Numbers**

Sales Drawing SD-120068-026-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

ZZCERT\_CE -

CER\_4000383479\_00\_000.pdf

Declaration of

Conformity

**Search Parts in this Series**

[120068 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1200680195](#) [884A30K05M003](#)