


KEMET, FLLD3-MH, EMI/RFI Filters, Noise Suppression, 520 VAC, 30 A, 240x50x85mm



General Information	
<b>Series:</b>	FLLD3-MH
<b>Style:</b>	Chassis Mount
<b>Description:</b>	EMI Filter, Chassis Mount, Motor Drives
<b>Features:</b>	Three Phase, High Performance, High Voltage
<b>RoHS:</b>	Yes
<b>Qualifications:</b>	IEC/EN 60939, UL 1283
<b>Lead:</b>	Threaded Studs M5

Dimensions	
<b>L</b>	240mm NOM
<b>W</b>	50mm NOM
<b>H</b>	85mm NOM
<b>L1</b>	255mm NOM
<b>L2</b>	270mm NOM
<b>W1</b>	30mm NOM
<b>J</b>	30mm NOM
<b>K</b>	5.5mm NOM
<b>M (Earth)</b>	Threaded Studs M5
<b>Lead</b>	Threaded Studs M5

Specifications	
<b>Voltage AC:</b>	520 VAC, 300 VAC
<b>Rated Frequency:</b>	50-60 Hz
<b>Ripple Current:</b>	30 A (50°C)
<b>Rated Temperature:</b>	50°C
<b>Temperature Range:</b>	-25/+100°C
<b>Climate Category:</b>	25/100/21
<b>Test Voltage DC (P to P):</b>	2250 VDC
<b>Test Voltage DC (P to E):</b>	3000 VDC
<b>Voltage:</b>	2250 VDC (Test P to P), 3000 VDC (Test P to E)
<b>Power Loss:</b>	12 W (25°C 50 Hz)
<b>Leakage Current:</b>	4.7 mA

Packaging Specifications	
<b>Packaging:</b>	Bulk
<b>Packaging Quantity:</b>	1
<b>Weight:</b>	1.1 kg