

416ERS6W



Products Low Voltage Products and Systems Industrial Plugs and Sockets Easy & Safe Surface Socket Outlets

General Information

Extended Product Type:	416ERS6W
Product ID:	2CMA101230R1000
EAN:	7392696012300
Catalog Description:	Surface socket outlets, 3P+N+E, 16 A, 346 ... 415 V
Long Description:	Surface socket outlets, 3P+N+E, IP67, 16 A, 346 ... 415 V

Additional Information

Additional Information:	3P+N+E
Cable Cross-Section:	1 ... 2.5 mm ²
Cable Diameter:	25 mm
Color:	Red
Connection Type:	Screw clamp
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85366990
Data Sheet, Technical Information:	2CMC700006C0201
Declaration:	2CMC700005D0001
Declaration of Conformity - CE:	2CMC700005D0001
Degree of Protection:	IP67
E-number:	2417625
EAC Certificate:	RU C-CZ.ME77.B.02742
EAN:	7392696012300
ETIM 5:	EC001321 - CEE socket outlet
ETIM 6:	EC001321 - CEE socket outlet
Enclosure Material:	Plastic (PA)
Environmental Information:	2CMC700001D0002
Frequency (f):	50 Hz 60 Hz
Function:	Surface socket outlet for wall mounting
Gross Weight:	0.3 kg
Housing Material:	Plastic (PA)
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#416ERS6W
Minimum Order Quantity:	5 piece
Number of Poles:	5
Package Level 1 EAN:	7392696020220
Package Level 1 Gross Weight:	1.5 kg
Package Level 1 Height:	467 mm
Package Level 1 Length:	177 mm
Package Level 1 Units:	5 piece
Package Level 1 Width:	134 mm
Product Main Type:	ERS
Product Name:	Surface outlet
Product Net Depth:	151 mm
Product Net Height:	119 mm
Product Net Length:	151 mm

Product Net Weight:	0.30 kg
Product Net Width:	89 mm
Protection Type:	Watertight
Rated Current (I_n):	16 A
Rated Voltage (U_r):	200/346 ... 240/415 V
SEMKO Certificate:	1616293
Selling Unit of Measure:	piece
Short Description:	Surface socket outlets, 3P+N+E, 16 A, 346 ... 415 V
Size:	150x89x117
Standards:	IEC 60309-1 IEC 60309-2
UNSPSC:	39120000
Clock Position Of Grounding Contact:	6 hour
RAL Number:	RAL 7012 - Basalt Grey
	<input type="text"/>