



PART NO.	MAX BUNDLE DIA.	LENGTH APPROX.	"A"±0.5	"B"±0.5	"C"±0.5	"W"±0.1	TENSILE STRENGTH	MATERIAL
MT-1	25 [1.00]	127 [5.00]	4.3 [.169]	6.4 [.252]	11.4 [.449]	4.6 [.181]	45 KG [100 LBS]	304 STAINLESS STEEL (RMS-381)
MT-2	51 [2.00]	201 [7.91]						
MT-3	70 [2.75]	259 [10.20]						
MT-4	102 [4.00]	362 [14.25]						
MT-5	152 [6.00]	521 [20.51]						
MT-6	203 [8.00]	679 [26.73]						
MT-7	254 [10.00]	838 [32.99]						
MT-8	304 [12.00]	998 [39.29]						
MT-9	380 [15.00]	1250 [49.21]						
MT-10	51 [2.00]	201 [7.91]	5.6 [.221]	10.2 [.402]	13.8 [.543]	7.9 [.311]	113 KG [250 LBS]	
MT-11	102 [4.00]	362 [14.25]						
MT-12	152 [6.00]	521 [20.51]						
MT-13	203 [8.00]	679 [26.73]						
MT-14	254 [10.00]	838 [32.99]						
MT-15	304 [12.00]	998 [39.29]						
MT-16	25 [1.00]	127 [5.00]	4.3 [.169]	6.4 [.252]	11.4 [.449]	4.6 [.181]	45 KG [100 LBS]	
MT-17	51 [2.00]	201 [7.91]						
MT-18	70 [2.75]	259 [10.20]						
MT-19	102 [4.00]	362 [14.25]						
MT-20	152 [6.00]	521 [20.51]						
MT-21	203 [8.00]	679 [26.73]						
MT-22	254 [10.00]	838 [32.99]						
MT-23	304 [12.00]	998 [39.29]						
MT-24	380 [15.00]	1250 [49.21]						
MT-25	51 [2.00]	201 [7.91]	5.6 [.221]	10.2 [.402]	13.8 [.543]	7.9 [.311]	113 KG [250 LBS]	
MT-26	102 [4.00]	362 [14.25]						
MT-27	152 [6.00]	521 [20.51]						
MT-28	203 [8.00]	679 [26.73]						
MT-29	254 [10.00]	838 [32.99]						
MT-30	304 [12.00]	998 [39.29]						

B	SEE CO 200322 FOR CHANGES	SK	02/09/09
A	RELEASED FOR PRODUCTION	SK	10.23.08
REV.	DESCRIPTION	ENGR.	DATE

TITLE: METAL TIES				DWG IN mm [IN]		FINAL	
CREATED USING SOLIDWORKS	FILE #: MT-X	DWN: SK	APP: S.K.	PART #			
GENERAL TOLERANCE UNLESS NOTED ±0.25 ANG.=±1°	SHEET: 1 OF 1	SHEET SIZE: B	DT: 05/13/08	CHKD: D.Z.	SEE TABLE		PRINT TYPE
RE: RICHCO, INC.			RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060				CA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[MT-7](#) [MT-4](#) [MT-29](#) [MT-30](#) [MT-5](#) [MT-9](#) [MT-24](#) [MT-17](#) [MT-8](#) [MT-23](#) [MT-26](#) [MT-6](#) [MT-1](#) [MT-10](#) [MT-11](#) [MT-12](#)
[MT-13](#) [MT-14](#) [MT-15](#) [MT-16](#) [MT-18](#) [MT-19](#) [MT-2](#) [MT-20](#) [MT-21](#) [MT-22](#) [MT-25](#) [MT-27](#) [MT-28](#) [MT-3](#)