



C1  
HAR-FLEX 26 POLE FEMALE CONNECTOR  
WITH STRAIN RELIEF

C2  
HAR-FLEX 26 POLE FEMALE CONNECTOR  
WITH STRAIN RELIEF

WIRING TABLE

C1	WIRE	C2
1	AWG 30	1
2	AWG 30	2
3	AWG 30	3
-	AWG 30	-
25	AWG 30	25
26	AWG 30	26

HARTING P/N	REVISION	Cable length ( L )
3315 243 010 0007	02	100 ± 3
3315 243 020 0008	02	200 ± 3
3315 243 050 0009	02	500 ± 5
3315 243 027 0034	02	270 ± 5
3315 243 060 0034	00	600 ± 10
3315 243 100 0034	00	1000 ± 10
3315 243 012 0034	00	120 ± 3
3315 243 017 0034	00	170 ± 3

NOTES:

- 1.)CABLE MUST BE PERFORMED 100% CONTINUITE TEST AND HI-POT(500VDC)TEST.
- 2.)CABLE OPERATION TEMPERATURE: -20°C TO +105°C
- 3.)CABLE SHOULD BE PACKED BY THE PLASTIC BAG,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION) EXPORT CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY.
- 4.)WHITE LABEL CONTENT:

DATA CODE  
HARTING P/N

	All rights reserved Department HCS - CN	Created by ZHENGL	Inspected by WANGE	Standardisation CHENJU	Date 2017-11-01	State Final Release
	Title Har-Flex 26 Pole,Dul-end,With SR,L=XX MM Type TB Number 33150003					Doc-Key / ECM-Nr. 100587128/UGD/000/G 500000127346
HARTING Customised Solutions D-32427 Minden						Rev. G Page 1/1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33152430100007](#) [33152430500009](#) [33152430200008](#)