

Product number: 037160



Description:

Brand:

Legrand

Series:

Viking3

Product Class:

Net Weight (kg):

0,007

Features

Connectable conductor cross section fine-strand without cable (mm ²):	0.25 - 2.5	Connectable conductor cross section solid-core (mm ²):	0.25 - 4
Connectable conductor cross section multi-wired (mm ²):	0.5 - 1	Rated current I _n (A):	24
Rated voltage (V):	500	Type of electrical connection 1:	Screw connection
Type of electrical connection 2:	Screw connection	Connection position:	Sideways
Number of levels:	1	Number of clamp positions per level:	2
Mounting method:	DIN rail (top hat rail) 35 mm	Material insulation body:	Other
Operation temperature (°C):	-5 - 40	Inflammability class of insulation material acc. with UL94:	V2
Width/grid dimension (mm):	52.2	Height at lowest possible mounting height (mm):	46.4
Explosion-tested version 'Ex e':	Yes	Closing plate required:	Yes
Colour:	Grey	Internally connected stages:	No
Height (mm):	46.4	Material:	Plastic
Surface treatment:	Polyamide		