

**ARCA 608030**



Sample photo

**Order symbol:** ARCA 608030  
**Product nbr:** 8120029  
**Description:** Cabinet, PC  
**Remarks:** Grey cover, 2-point locking, hinges on the short side

**EAN:** 6418074085160  
**EI. number:**  
 Finland: 3424064  
 Denmark: 8212095368  
 Sweden: 2500121  
 Norway:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.  
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		600	800	300	Ingress Protection (EN 60529): IP 66
<b>inch:</b>		23.6	31.5	11.8	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
Materials:					
<b>Material:</b>		Polycarbonate			
<b>Base colour:</b>		RAL 7035			
<b>Cover colour:</b>		RAL 7035			
<b>Gasket material:</b>		PUR			
Temperatures:					
<b>Short term:</b>		-40 ... 120 °C			
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		-40 ... 175 °F			
Accessories:					
MPP ARCA 8060		Mounting plate perforated			
MPS ARCA 8060		Mounting plate			
MPX ARCA 8060		Mounting plate			
PMK ARCA 80		Pole mounting kit			
					Certificates:
					Fimko

ARCA 800x600x300

ARCA 600x800x300

