


Neodymium Shallow Pot Magnet - datasheet

Threaded hole

- Neodymium iron boron 'rare earth' material
- Strongest magnet material available
- 80°C max. operating temp.
- High resistance to de-magnetisation
- N35 grade
- Zinc plated body



Product Information

Product No.	Diameter	Pot height	Total height	Thread size	Ferrule outer dia.	Weight	Pull force
	mm					kg	
E775NEO	20	6	13	M4	8	0.0165	14
E777NEO	32	7	15.5	M5	10	0.048	35